






1:100 Scale





CRS-22 iROSA panel
Deployed configuration
P6 truss

Print on Cardstock (90 lbs)

PRINT X 2




Roll this piece on a cotton swab (2.5 mm thick)







1:100 Scale





CRS-26 iROSA panel
Deployed configuration
4A - 3A channels

Print on Cardstock (90 lbs)

PRINT X 2




Roll this piece on a cotton swab (2.5 mm thick)







1:100 Scale



CRS-28 iROSA panel
Deployed configuration
1A - 1B channels

Print on Cardstock (90 lbs)

PRINT X 2



Roll this piece on a cotton swab (2.5 mm thick)

